


Buyers of this company:



www.LogoWow.net



OPTC



دانشگاه زنجان



دانشگاه ارومیه



دانشگاه محقق اردبیلی



دانشگاه حکیم سبزواری



دانشگاه بوعلی سینا

OPTC

Types of Spectrometer Models with Prices and Applications:

Application:

Light source emission

Coating Thickness Measurement

Absorption measurement

Transmission measurement

Reflection measurement

Diffuse reflection

Fluorescence more

Raman

Plasma

Lumens measurement


Color measurement

OPTC

Spectrophotometer BELNA

Specification

CCD sensor	Toshiba TCD1304DG
Measuring range	200-1100nm
Resolution	1.8nm
Slit	25um
Pixel	3648
Pixel size	8um x 200um
Pixel depth	100,000 electrons
Signal to noise ratio	800: 1
Exposure time	10us - 60s
A / D resolution	16 bit
Weight	8 kg
Dimensions	102mm * 84mm *59mm +90mm * 80mm * 31mm
External trigger	yes
Maximum temperature	32 C
Power	AC-DC transformer, 100 - 240 VAC, Voltage output: 12 VDC
Light source	10W Halogen lamp+30W Deuterium lamp-light source LED



Spectrometer & light source



[Tel:03155579058](tel:03155579058)

Mobile: 09136425874

Email:optcompany@yahoo.com

OPTC

Software:




[Tel:03155579058](tel:03155579058)

Mobile: 09136425874

Email:optcompany@yahoo.com

OPTC



OPTC

Light source halogen deuterium spectrum

