



## UV-Vis Array Spectrophotometer



- Simultaneous obtained of all spectra
- Integration time controlling using software
- Mathematical processing (Averaging, Sum, Smooth . . .)
- Time Monitoring of spectra
- Standard Wavelength calibration of spectrophotometer



## Specifications of Array Spectrophotometer

Optical Specifications	
Wavelength range	200-800 nm
Straylight	< 0.03%
Resolution	< + 1.0 nm
Wavelength Accuracy	< ± 0.1 nm
Wavelength Reproducibility	< ± 0.02 nm for 10 consecutive scans (NIST 2034)
Photometric Accuracy	< ± 0.01 A at 440.0 465.0 590.0 635.0 nm(NIST 930e)
Photometric noise	<0.01 A 80 scan at 0 A, 500 nm
Photometric stability	<0.01 A/min at 0 A, 500 nm
Baseline flatness	<0.01A 0.5 second blank, 0.5 second scan at 0 A, 500 nm
Scan time	2-1000 ms
Typical Scan Time	0.05 s
Light Source	Deuterium + Halogen /Tungsten lamp
Detector	2000 Multichannel
Physical Specifications	
Communication	USB 2
Software	Windows XP , 7, 8
Height × width × depth	14 × 33 × 50 cm
Weight	10 kg
Power	220V AC 50/60 HZ

Tell : (021)88357692  
Fax : (021)88357803

Address : No.115, Dr. Fathi shaghghi St, Yosef abad, Tehran, Iran

Email : info@spectrometer.ir  
Website : www.spectrometer.ir

